

[Afficher tous les 27 produits de la même famille.](#)

## Monture Optique de Démarrage Rapide, Monture de Polariseur, 25,4 mm avec Micromètre



#17-534 and #17-513



+5

Stock **#17-525** FIN DE SÉRIE CONTACT

-

1

+

€513<sup>75</sup>

AJOUTER AU PANIER

| Prix sur Quantité |                                  |
|-------------------|----------------------------------|
| Qté 1+            | €513,75 prix unitaire            |
| Need More?        | <a href="#">Demande de Devis</a> |

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

| Caractéristiques du produit |                 |
|-----------------------------|-----------------|
| Adjustable - Rotary         | Type:           |
| Circular                    | Type d'Optique: |
| Contenu du Coffret:         |                 |
| #55-011, #16-322, #15-849   |                 |

| Propriétés physiques et mécaniques |                                |  |
|------------------------------------|--------------------------------|--|
| 22.0                               | Ouverture Utile CA (mm):       |  |
| 5 arcminutes                       | Incréments:                    |  |
| 360                                | Rotation Grossière (°):        |  |
| ±5                                 | Rotation Fine (°):             |  |
| 127.00                             | Hauteur de l'axe optique (mm): |  |
| 25.4                               | Post Diameter (mm):            |  |

| Connectivité matérielle & interfaçage |            |  |
|---------------------------------------|------------|--|
| Micrometer                            | Mécanisme: |  |

| Filetage & montage |                                       |  |
|--------------------|---------------------------------------|--|
| 25.0 - 25.4        | Taille des optiques compatibles (mm): |  |
| 7.0 (Max.)         | Épaisseur d'Optique Compatible (mm):  |  |
| M6 x 1.0           | Compatible Post:                      |  |
| Polarizer          | Type of Mounting Optics:              |  |

| Conformité réglementaire |                             |  |
|--------------------------|-----------------------------|--|
| Conforme                 | RoHS 2015:                  |  |
| Visionner                | Certificate of Conformance: |  |
| Conforme                 | Reach 233:                  |  |

## Description produit

- Hauteurs communes des axes optiques de 5" (127 mm) pour une intégration rapide dans des systèmes
- Montures optiques et tiges à pied combinées offertes à un prix réduit de 5%
- Idéales pour la mise en place de nouveaux systèmes optiques de paillasse

Les Montures Optiques de Démarrage Rapide sont conçues avec une hauteur d'axe optique commune de 127 mm (5") à partir de la surface de la table de laboratoire, et combinent tout le matériel de montage nécessaire pour une intégration facile dans des systèmes. Grâce aux Montures Optiques de Démarrage Rapide conçues pour une grande variété de composants optiques, les systèmes et les expériences complexes peuvent être facilement organisés sans qu'il soit nécessaire de procéder à un réglage important des axes optiques. Les Montures Optiques de Démarrage Rapide sont idéales pour mettre en place rapidement et facilement de nouveaux systèmes optiques de paillasse avec les montures essentielles d'Edmund Optics telles que les [Montures de Miroirs Optiques Cinématiques E-Series](#), les [Montures de Miroirs Optiques Cinématiques TECHSPEC](#), les [Montures Compactes pour Miroirs & Lentilles](#), et les [Montures de Composants Optiques](#).

## Informations techniques

| Kit Stock No. | Kit Description                                                                     | Contents of Kit                                                                                                                                                                                                                                                                    |
|---------------|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| #17-513       | 25.0/25.4mm Optic Diameter, X-Y Translating Quick Start Optical Mounts              | <a href="#">#62-956</a> : 25.0/25.4mm Optic Dia., X-Y Translating Optic Mount<br><a href="#">#16-460</a> : Pedestal Extender 20.8mm, M6, 8-32<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                          |
| #17-514       | 50.0/50.8mm Optic Diameter, X-Y Translating Optic Mount, Quick Start Optical Mounts | <a href="#">#62-957</a> : 50.0/50.8mm Optic Dia., X-Y Translating Optic Mount<br><a href="#">#16-317</a> : Pedestal Extender 8.0mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                           |
| #17-515       | 25.4mm Optic Dia., Fixed Optic Mount, Quick Start Optical Mounts                    | <a href="#">#64-561</a> : 25.4mm Optic Dia., 10mm Max Optic Thickness, Optic Mount<br><a href="#">#16-305</a> : Pedestal Shim 5/32" (3.97mm)<br><a href="#">#16-333</a> : 12.5mm Length 1/4"-20, #8-32 Thread Adapter<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm |
| #17-516       | 50.0mm Optic Dia., Fixed Optic Mount, Quick Start Optical Mounts                    | <a href="#">#64-567</a> : 50.0mm Optic Dia., Optic Mount<br><a href="#">#16-321</a> : Pedestal Extender 16.8mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                               |
| #17-517       | 25/25.4mm ID, Precision Gimbal Mount, Quick Start Optical Mounts                    | <a href="#">#54-999</a> : 25.0/25.4mm Optic Dia., Precision Gimbal Mount<br><a href="#">#16-308</a> : Pedestal Shim 1/16" (1.59mm)<br><a href="#">#16-329</a> : 10.5mm Length M6, #8-32 Thread Adapter<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                 |

|         |                                                                                            |                                                                                                                                                                                                                                                                                    |
|---------|--------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| #17-518 | 50/50.8mm ID, Precision Gimbal Mount, Quick Start Optical Mounts                           | <a href="#">#55-000</a> : 50.0/50.8mm Optic Dia., Precision Gimbal Mount<br><a href="#">#16-310</a> : Pedestal Shim 1/64" (0.40mm)<br><a href="#">#16-321</a> : Pedestal Extender 16.8mm, 8-32, M6<br><a href="#">#15-848</a> : Pedestal Post, English, 50.8mm                     |
| #17-519 | 25.0/25.4mm Optic Dia., Kinematic Mirror Mount with Micrometer, Quick Start Optical Mounts | <a href="#">#55-456</a> : 25.0/25.4mm Optic Dia., Kinematic Mirror Mount with Micrometer<br><a href="#">#16-319</a> : Pedestal Extender 14.0mm, 8-32, M6<br><a href="#">#16-309</a> : Pedestal Shim 1/32" (0.79mm)<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm     |
| #17-520 | 50.0/50.8mm Optic Dia., Kinematic Mirror Mount with Micrometer, Quick Start Optical Mounts | <a href="#">#56-326</a> : 50.0/50.8mm Optic Dia., Kinematic Mirror Mount with Micrometer<br><a href="#">#16-304</a> : Pedestal Shim 3/16" (4.76mm)<br><a href="#">#16-331</a> : 15.0mm Length M6, #8-32 Thread Adapter<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm |
| #17-521 | 25/25.4mm Diameter, E-Series Kinematic Mount, Quick Start Optical Mounts                   | <a href="#">#15-866</a> : 25.0/25.4mm Optic Dia., E-Series Kinematic Mount<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm                                                                                                                                            |
| #17-522 | 50/50.8mm Diameter, E-Series Kinematic Mount, Quick Start Optical Mounts                   | <a href="#">#15-867</a> : 50.0/50.8mm Optic Dia., E-Series Kinematic Mount<br><a href="#">#15-857</a> : Pedestal Extender, English, 76.2mm<br><a href="#">#15-845</a> : Pedestal Post, English, 12.7mm                                                                             |
| #17-523 | 25/25.4mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts                      | <a href="#">#58-854</a> : 25.0/25.4mm Optic Dia., Kinematic Mount, 3-Screws<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm                                                                                                                                           |
| #17-524 | 50/50.8mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts                      | <a href="#">#58-855</a> : 50.0/50.8mm Optic Dia., Kinematic Mount, 3-Screws<br><a href="#">#15-857</a> : Pedestal Extender, English, 76.2mm<br><a href="#">#15-845</a> : Pedestal Post, English, 12.7mm                                                                            |
| #17-525 | 25.4mm w/ micrometer, Polarizer Mount, Quick Start Optical Mounts                          | <a href="#">#55-011</a> : 25.4mm w/ micrometer, Polarizer Mount<br><a href="#">#16-322</a> : Pedestal Extender 18.0mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                        |
| #17-526 | 50.0mm w/ micrometer, Polarizer Mount, Quick Start Optical Mounts                          | <a href="#">#56-329</a> : 50.0mm w/ micrometer, Polarizer Mount<br><a href="#">#16-317</a> : Pedestal Extender 8.0mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                         |
| #17-527 | 50mm Cube, Prism Mount Metric, Quick Start Optical Mounts                                  | <a href="#">#55-013</a> : 50mm Diameter, Prism Mount Metric<br><a href="#">#16-322</a> : Pedestal Extender 18.0mm, 8-32, M6<br><a href="#">#16-309</a> : Pedestal Shim 1/32" (0.79mm)<br><a href="#">#15-848</a> : Pedestal Post, English, 50.8mm                                  |
| #17-528 | 50mm Cube Rotary Mount with Prism Holder, Quick Start Optical Mounts                       | <a href="#">#53-027</a> : Rotary Mount with Prism Holder<br><a href="#">#16-325</a> : Pedestal Extender 18.0mm, 8-32, 1/4"-20<br><a href="#">#15-848</a> : Pedestal Post, English, 50.8mm                                                                                          |
| #17-529 | 2"/50.8mm Square, Bar Clamp, Quick Start Optical Mounts                                    | <a href="#">#54-995</a> : 60mm sq - Rectangular Bar Clamp<br><a href="#">#16-318</a> : Pedestal Extender 11.0mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                              |
| #17-530 | 2"/50.8mm Diameter, Bar Type Lens / Filter Holder, Quick Start Optical Mounts              | <a href="#">#03-669</a> : 7.0 - 67.0 Optic Height, English Bar-Type Optic Holder<br><a href="#">#16-323</a> : Pedestal Extender 11.0mm, 8-32, 1/4"-20<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                  |
| #17-531 | 2"/50.8mm Square, Spring Mount Filter Holder, Quick Start Optical Mounts                   | <a href="#">#55-531</a> : Spring Mount Filter Holder, Metric<br><a href="#">#16-320</a> : Pedestal Extender 16.0mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                           |
| #17-532 | 30mm Dia., Multiple Filter Holder, Quick Start Optical Mounts                              | <a href="#">#55-006</a> : 30mm, Multiple Filter Holder<br><a href="#">#16-321</a> : Pedestal Extender 16.8mm, 8-32, M6<br><a href="#">#15-849</a> : Pedestal Post, English, 76.2mm                                                                                                 |
| #17-533 | 25mm Dia., Manual Filter Wheel, Quick Start Optical Mounts                                 | <a href="#">#34-545</a> : Manual Cage Filter Wheel<br><a href="#">#16-329</a> : 10.5mm Length M6, #8-32 Thread Adapter<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm                                                                                                |
| #17-534 | 25.4mm Optic Dia., Thin Mirror Mount, M4, Quick Start Optical Mounts                       | <a href="#">#13-590</a> : 25.4mm Optic Dia., Thin Mirror Mount M4<br><a href="#">#15-844</a> : Pedestal Post, Metric, 101.6mm                                                                                                                                                      |
| #17-535 | 25.4mm Optic Dia., Thin Mirror Mount, 8-32, Quick Start Optical Mounts                     | <a href="#">#13-591</a> : 25.4mm Optic Dia., Thin Mirror Mount, 8-32<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm                                                                                                                                                  |
| #17-536 | 25.0/25.4mm Optic Dia., SM1 Thin Mount, M4, Quick Start Optical Mounts                     | <a href="#">#13-787</a> : 25.0/25.4mm Optic Dia., SM1 Thin Mount, M4<br><a href="#">#15-844</a> : Pedestal Post, Metric, 101.6mm                                                                                                                                                   |
| #17-537 | 25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32, Quick Start Optical Mounts                   | <a href="#">#13-788</a> : 25.0/25.4mm Optic Dia., SM1 Thin Mount, 8-32<br><a href="#">#15-850</a> : Pedestal Post, English, 101.6mm                                                                                                                                                |