

[Afficher tous les 23 produits de la même famille.](#)

Composant en Ligne InfiniTube FM, Objectifs +10X

See More by [Infinity Photo-Optical Company](#)



InfiniTube FM In-Line Attachment, +10X Objectives, #58-312

Stock **#58-312** 1 In Stock

-

1

+

€835^{,00}

AJOUTER AU PANIER

Prix sur Quantité	
Qté 1+	€835,00 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

Lens Accessory	Type:
----------------	-------

Conformité réglementaire

Conforme	RoHS 2015:
Conforme	Reach 224:

- Directement sur caméras CCD à monture C et de formats 2/3" et moindre
- Focalisation interne

Les Systèmes InfiniTube™: FMest utilisé pour monter des objectifs conjugués à l'infini sur des caméras CCD, amenant des grossissements impossibles avec des objectifs ordinaires, tel qu'un grossissement 50X. Le système InfiniTube™ peut être configuré dans une large variété. Il peut être utilisé tout seul (InfiniTube™ #58-310 ou #58-309) pour des applications où l'illumination est produite à partir d'une autre source telle qu'un backlight ou d'une illumination directionnelle. Le Système InfiniTube™ FM peut aussi être configuré pour une illumination in-line avec des attachements. Le premier attachement in-line (#58-313) fut conçu pour des objectifs ayant un grossissement 10X ou moindre et n'est pas conseillé pour des hautes puissances. Le second attachement in-line (#58-312) fut conçu pour fonctionner avec un efficacité supérieure lorsque utilisé avec des grossissements 10X ou plus, mais peut être utilisé avec tous grossissements. Tous les accessoires en ligne acceptent nos [Guides de Lumière à Fibre Optique](#) avec un diamètre de pointe de 0,312".

Note: **Système standard** pour capteurs 2/3" est toujours disponible.

DL Doubler Tube (2X) (#39-686)

C-Clamp w/ 1/4" =20 Mounting Hole (#57-788)

InfiniTube™ FM-100 (#58-309)

InfiniTube™ FM-200 (#58-310)

InfiniTube™ In-Line Attachment Optimized for 2X to 10X Objectives (#58-313)

InfiniTube™ In-Line Attachment Optimized for 10X and higher Objectives (#58-312)

Collector II-HM (#59-472)

Olympus US Objective Adapter (RMS) (#58-314)

Nikon CF160 Objective Adapter (M25) (#58-315)

Mitutoyo/Achrovid™ Objective Adapter (M26) for 2X Objectives (#58-949)

PL/FD Objectives

- #59-115: PL/FD-195mm WD/0.25X
- #59-116: PL/FD-295mm WD/0.165X
- #59-117: PL/FD-390mm WD/0.125X

Objective Adapter (M26) (#58-316)

PL Objectives

- #55-402: PL-1.8mm WD/2.00X
- #55-403: PL-4.4mm WD/1.00X
- #55-404: PL-9.4mm WD/0.66X
- #55-405: PL-9.4mm WD/0.50X

All-thread 1/8" 20 TPI 3.00" Length

Mitutoyo/Achrovid™ Objective Adapter (M26) for 2X Objectives

Note: The PL-Series Objectives are specifically designed to be used directly (no adapters required) with the InfiniTube™ FM-Series Main Bodies

All PL-Series Objectives are amplified by 2X (InfiniTube™ FM-100) or 4X (InfiniTube™ FM-200) their engraved initial power ratings.

A DL 2X Tube can be used atop InfiniTube™ FM-Series Main Bodies to further amplify magnification by a 2X factor.

System Includes	Stock No.
InfiniTube In-Line Assembly Unit	#58-311
Hitachi KP-D20B Camera	#55-837
15.1" Diagonal LCD Monitor (US version only)	#56-522
Y-C Cable (6 ft.)	#39-255
Mitutoyo/Achrovid™ Objective Adapter	#58-316
M-150 Fiber Optic Illuminator	#55-718
Fiber Optic Light Guide (48" L)	#39-367
Fiber Optic Adapter	#38-944
Standard Boom Stand	#54-120
Rack & Pinion Mounting Plate	#54-123
C-Clamp with ¼-20 Munting Hole	#57-788