

[Afficher tous les 9 produits de la même famille.](#)

M62 x 0,75 Filetage, Adaptateur Fileté pour Anneaux Lumineux



Ring Light Filter Thread Adapter. Filter Thread varies by Stock Number. (M30.5 x0.5 Thread Shown)

Stock **#56-099** FIN DE SÉRIE **7 In Stock**

⊖ 1 ⊕ €45⁹⁵

AJOUTER AU PANIER

Prix sur Quantité	
Qté 1+	€45,95 prix unitaire
Need More?	Demande de Devis

ⓘ Les prix sont indiqués hors TVA et droits applicables.

Espace téléchargement

Caractéristiques du produit

Accessory **Type d'Éclairage:**

Propriétés physiques et mécaniques

Anodized Aluminum **Construction:**

Filetage & montage

M62.0 x0.75 **Filetage Filtre:**

Conformité réglementaire

[Conforme](#) **RoHS 2015:**

[Visionner](#) **Certificate of Conformance:**

[Conforme](#) **Reach 235:**

Description produit

- Compatibles avec les [Anneaux Lumineux LED](#)
- Filetages de Dimension Usuelle Disponibles
- Facilitent l'Intégration des Anneaux Lumineux LED

Les Adaptateurs Filetés à Anneaux Lumineux permettent à nos [Anneaux Lumineux LED](#) de se connecter directement aux [Objectifs d'Imagerie](#). L'adaptateur se glisse dans une bride situé à l'arrière de l'anneau lumineux. Il est recommandé de sélectionner l'adaptateur de l'anneau lumineux avec le filetage correspondant au filetage du filtre avant de l'objectif. Tous les adaptateurs disposent d'une construction en aluminium anodisé.

Remarque : Bien que les adaptateurs de filetage à anneaux lumineux puissent se monter sur une large variété d'objectifs d'imagerie, la distance de travail et la couverture de champ fournis par l'anneau lumineux LED sont à considérer pour une intégration système appropriée.

Informations techniques

Filter Thread	Imaging Lenses Available to Use with Adapters	Adapter Stock No.
M25.5 x 0.5	8.5/12/16/25/35/50/75mm C Series Fixed Focal Length Lenses	#56-523
M30.5 x 0.5	18mm and 25mm DG Series FFL , 28mm Rodagon , MegaPixel Fixed Focal Length (vignetting may occur with large format sensors), Compact VIS-NIR Lenses (vignetting may occur with large format sensors)	#56-089
M34.5 x 0.5	3.3X Macro Zoom Lens	#56-090
M37 x 0.75	MMS® , 35mm DG Series FFL , 0.50X and 1.0X SilverTL™ Telecentric	#56-091
M39 x 0.5	50mm DG Series FFL	#56-092
M40.5 x 0.5	7X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), 35/50/60/80/105/135mm Rodagon Lenses , 0.60X SilverTL™ Telecentric Lenses	#56-093
M43 x 0.75	55mm Telecentric , 0.30X/0.40X/2.0X SilverTL™ Telecentric	#56-094
M46 x 0.75	10X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), 0.25X SilverTL™ Telecentric	#56-095
M49 x 0.75	75mm DG Series FFL	#56-096
M52 x 0.75	6X Close Focus Zoom (vignetting may occur with large format sensors or at lowest zoom settings), TECHSPEC® LS Series Fixed Focal Length Lenses	#56-097
M58 x 0.75	0.36X/0.5X GoldTL™ Telecentric , 0.20X/4.0X SilverTL™ Telecentric	#56-098
M62 x 0.75	0.73X/1X GoldTL™ Telecentric , 0.16X SilverTL™ Telecentric	#56-099
M72 x 0.75	0.18X/0.25X GoldTL™ Telecentric	#56-100

Compatible Ring Lights

[Advanced Illumination Standard Working Distance LED Ring Lights](#)

[Advanced Illumination Extended Working Distance LED Ring Lights](#)

[Advanced Illumination Brightfield/Darkfield LED Ring Lights](#)

[Advanced Illumination 5" Darkfield LED Illuminators](#)